

Bellco Glass, Inc.
Specification Sheet
For Product #: 1965-83000

Description: 3000mL Bell-Flo™ Spinner Flask

Flask Specifications:

Material: Type 1 Class A Borosilicate Glass

Dimensions: 165mm OD x 290mm Overall Height, 252.7mm across sidearms


Two 45mm sidearms angled 53° off the centerline

One 100mm Screw Thread Center Neck

Indented Bottom: Prevents dead spot under impeller

Side Baffles: Three equally spaced baffles, 100mm long x 9mm deep

Supply with: Two 45mm PP Blue Screw Caps & PP Blue Pouring Rings



The information contained in this specification sheet we believe is correct to the best of our knowledge. The recommendations and suggestions herein are made without guarantee or representation as to results. We recommend that adequate tests be made in your laboratory or plant to determine if this product meets all of your requirements.



BELLCO GLASS, INC.



Bellco Glass, Inc. · 340 Edrudo Road · Vineland, NJ · 08360

Ver: 7/05