

Bellco Glass, Inc.
Specification Sheet
Product #: 1965-92002

Description: Glass Ball Spinner Comp, 250mL

Size: 250mL

Material: Type 1 Class A Borosilicate Glass


Flask Dimensions: 85mm OD x 140mm OAH, two 32mm sidearms offset at 55°, 70mm center neck

Includes two 32mm blue PP screw caps & two 32mm blue PP pouring rings

Impeller Assembly: one 70mm blue PP screw cap, 70mm Teflon cap seal, 70mm blue silicone sealing gasket, soft silicone flex tube, glass ball magnet tube, and magnet

Specially Formed Bottom Indent Prevents Accumulation under impeller

Glass ball houses a magnet for gentle agitation of Micro carrier Beads



The information contained in this specification sheet we believe is correct to the best of our knowledge. The recommendations and suggestions herein are made without guarantee or representation as to results. We recommend that adequate tests be made in your laboratory or plant to determine if this product meets all of your requirements.



BELLCO GLASS, INC.



Bellco Glass, Inc. · 340 Edrudo Road · Vineland, NJ · 08360

Ver: 7/05