

Bellco Glass, Inc.
Specification Sheet
Product #: 1965-92010

Description: Glass Ball Spinner Comp, 1000mL

Size: 1000mL

Material: Type 1 Class A Borosilicate Glass


Flask Dimensions: 135mm OD x 240mm OAH, two 45mm sidearms offset at 60°, 100mm center neck

Includes two 45mm blue PP screw caps & two 45mm blue PP pouring rings

Impeller Assembly: one 100mm blue PP screw cap, 100mm Teflon cap seal, 100mm blue silicone sealing gasket, soft silicone flex tube, glass ball magnet tube, and magnet

Specially Formed Bottom Indent Prevents Accumulation under impeller

Glass ball houses a magnet for gentle agitation of Micro carrier Beads



The information contained in this specification sheet we believe is correct to the best of our knowledge. The recommendations and suggestions herein are made without guarantee or representation as to results. We recommend that adequate tests be made in your laboratory or plant to determine if this product meets all of your requirements.



BELLCO GLASS, INC.



Bellco Glass, Inc. · 340 Edrudo Road · Vineland, NJ · 08360

Ver: 7/05