

**Bellco Glass, Inc.**  
**Specification Sheet**  
**Product #: 1965-92030**

**Description: Glass Ball Spinner Comp, 3000mL**

**Size: 3000mL**

**Material: Type 1 Class A Borosilicate Glass**


**Flask Dimensions: 165mm OD x 290mm OAH, two 45mm sidearms offset at 53°, 100mm center neck**

**Includes two 45mm blue PP screw caps & two 45mm blue PP pouring rings**

**Impeller Assembly: one 100mm blue PP screw cap, 100mm Teflon cap seal, 100mm blue silicone sealing gasket, soft silicone flex tube, glass ball magnet tube, and magnet**

**Specially Formed Bottom Indent Prevents Accumulation under impeller**

**Glass ball houses a magnet for gentle agitation of Micro carrier Beads**



**The information contained in this specification sheet we believe is correct to the best of our knowledge. The recommendations and suggestions herein are made without guarantee or representation as to results. We recommend that adequate tests be made in your laboratory or plant to determine if this product meets all of your requirements.**



**BELLCO GLASS, INC.**



Bellco Glass, Inc. · 340 Edrudo Road · Vineland, NJ · 08360

Ver: 7/05