

**Bellco Glass, Inc.**  
**Specification Sheet**  
**Product #: 1965-94010**

**Description: Glass Ball Spinner Flask Only**

**Size: 100mL**

**Material: Type 1 Class A Borosilicate Glass**

**Dimensions: 63.5mm OD x 135mm Overall Height, 145mm across sidearms**


**Two 32mm Sidearms angled 55° offset center**

**70mm Screw Thread Center Neck**

**Dimpled Bottom**

**Graduations: 20mL to 100mL, every 20mL – White Ink (Approx Volumes)**

**Supply with: Two 32mm PP Blue Screw Caps & PP Blue Pouring Rings**



**The information contained in this specification sheet we believe is correct to the best of our knowledge. The recommendations and suggestions herein are made without guarantee or representation as to results. We recommend that adequate tests be made in your laboratory or plant to determine if this product meets all of your requirements.**



**BELLCO GLASS, INC.**



Bellco Glass, Inc. · 340 Edrudo Road · Vineland, NJ · 08360

Ver: 7/05