

Bellco Glass, Inc.
Specification Sheet
Product #: 1965-94025

Description: Glass Ball Spinner Flask Only

Size: 250mL

Material: Type 1 Class A Borosilicate Glass

Dimensions: 85mm OD x 140mm Overall Height, 164mm across sidearms


Two 32mm Sidearms angled 55° offset center

70mm Screw Thread Center Neck

Dimpled Bottom

Graduations: 50mL to 250mL, every 25mL – White Ink (Approx Volumes)

Supply with: Two 32mm PP Blue Screw Caps & PP Blue Pouring Rings



The information contained in this specification sheet we believe is correct to the best of our knowledge. The recommendations and suggestions herein are made without guarantee or representation as to results. We recommend that adequate tests be made in your laboratory or plant to determine if this product meets all of your requirements.



BELLCO GLASS, INC.



Bellco Glass, Inc. · 340 Edrudo Road · Vineland, NJ · 08360

Ver: 7/05