

Bellco Glass, Inc.
Specification Sheet
Product #: 1965-94100

Description: Glass Ball Spinner Flask Only

Size: 1000mL

Material: Type 1 Class A Borosilicate Glass

Dimensions: 135mm OD x 240mm Overall Height, 250mm across sidearms


Two 45mm Sidearms angled 60° offset center

100mm Screw Thread Center Neck

Dimpled Bottom

Graduations: 100mL to 1000mL, every 100mL – White Ink (Approx Volumes)

Supply with: Two 45mm PP Blue Screw Caps & PP Blue Pouring Rings



The information contained in this specification sheet we believe is correct to the best of our knowledge. The recommendations and suggestions herein are made without guarantee or representation as to results. We recommend that adequate tests be made in your laboratory or plant to determine if this product meets all of your requirements.



BELLCO GLASS, INC.



Bellco Glass, Inc. · 340 Edrudo Road · Vineland, NJ · 08360

Ver: 7/05