

Bellco Glass, Inc.
Specification Sheet
Product #: 1965-94600

Description: Glass Ball Spinner Flask Only

Size: 6000mL

Material: Type 1 Class A Borosilicate Glass

Dimensions: 204mm OD x 410mm Overall Height, 268mm across sidearms


Two 45mm Sidearms angled 30° offset center

100mm Screw Thread Center Neck

Dimpled Bottom

Graduations: 1L to 6L, every 1L – White Ink (Approx Volumes)

Supply with: Two 45mm PP Blue Screw Caps & PP Blue Pouring Rings



The information contained in this specification sheet we believe is correct to the best of our knowledge. The recommendations and suggestions herein are made without guarantee or representation as to results. We recommend that adequate tests be made in your laboratory or plant to determine if this product meets all of your requirements.



BELLCO GLASS, INC.



Bellco Glass, Inc. · 340 Edrudo Road · Vineland, NJ · 08360

Ver: 7/05