

Bellco Glass, Inc.
Specification Sheet
Product #: 1965-94800

Description: Glass Ball Spinner Flask Only

Size: 8000mL

Material: Type 1 Class A Borosilicate Glass

Dimensions: 238mm OD x 420mm Overall Height, 270mm across sidearms

Two 45mm Sidearms angled 30° offset center

100mm Screw Thread Center Neck

Dimpled Bottom

Graduations: 500mL to 8000mL, every 500mL – White Ink (Approx Volumes)

Supply with: Two 45mm PP Blue Screw Caps & PP Blue Pouring Rings



The information contained in this specification sheet we believe is correct to the best of our knowledge. The recommendations and suggestions herein are made without guarantee or representation as to results. We recommend that adequate tests be made in your laboratory or plant to determine if this product meets all of your requirements.



BELLCO GLASS, INC.



Bellco Glass, Inc. · 340 Edrudo Road · Vineland, NJ · 08360

Ver: 7/05