

Bellco Glass, Inc.
Specification Sheet
Product #: 1965-95025

Description: Glass Ball Impeller Assembly Only

Size: 250mL


Screw Cap: Blue PP, 70mm OD x 22.4mm T

Cap Seal: Teflon, 67.9mm OD x 9.1mm T

Sealing Ring: Blue silicone rubber, 66.7mm OD x 47.6mm ID x 4.76mm T

Flex Tube: Soft silicone, 41.3mm OAL, 0.312" OD x 0.248" ID

Magnet Tube: Type 1 Class A Borosilicate Glass, 95mm OAL, 28mm OD ball, houses one cast alnico magnet



The information contained in this specification sheet we believe is correct to the best of our knowledge. The recommendations and suggestions herein are made without guarantee or representation as to results. We recommend that adequate tests be made in your laboratory or plant to determine if this product meets all of your requirements.



BELLCO GLASS, INC.



Bellco Glass, Inc. · 340 Edrudo Road · Vineland, NJ · 08360

Ver: 7/05