

Bellco Glass, Inc.
Specification Sheet
Product #: 1965-95300

Description: Glass Ball Impeller Assembly Only

Size: 3000mL


Screw Cap: Blue PP, 100mm OD x 22.4mm T

Cap Seal: Teflon, 95.3mm OD x 10.4mm T

Sealing Ring: Blue silicone rubber, 91.4mm OD x 76.2mm ID x 6.1mm T

Flex Tube: Soft silicone, 76.2mm OAL, 0.312" OD x 0.248" ID

Magnet Tube: Type 1 Class A Borosilicate Glass, 216mm OAL, 34mm OD ball, houses one cast alnico magnet



The information contained in this specification sheet we believe is correct to the best of our knowledge. The recommendations and suggestions herein are made without guarantee or representation as to results. We recommend that adequate tests be made in your laboratory or plant to determine if this product meets all of your requirements.



BELLCO GLASS, INC.



Bellco Glass, Inc. · 340 Edrudo Road · Vineland, NJ · 08360

Ver: 7/05