

HI98192

## Professional Waterproof Meters

EC/TDS/Resistivity/Salinity Meter with USP <645>

- **Waterproof**
  - IP67 rated waterproof, rugged enclosure
- **Salinity readings**
  - Salinity can be displayed as % NaCl, seawater scale (ppt) or practical salinity scale (PSU)
- **Calibration**
  - Perform up to a five point calibration for enhanced accuracy
- **Temperature compensation**
  - Automatic Temperature Compensation
  - Configurable temperature coefficient range from 0.00 to 10.00%/°C
- **Four-ring platinum probe**
  - This probe can cover low EC samples to 1000 mS/cm (actual EC)
- **Approximately 100 hour battery life**
  - Powered by (4) 1.5V AA batteries
- **Clear display**
  - Dot matrix display with multifunction virtual keys
- **AutoHold**
  - Automatically holds the first stable reading on the display
- **Calibration timeout**
  - Alerts when calibration is due at a specified interval
- **Connectivity**
  - PC connectivity via opto-isolated micro-USB with HI92000 software
- **GLP**
  - GLP data provides data from previous calibration to ensure Good Laboratory Practices are met
- **Intuitive keypad**
  - Most of the available options such as GLP information, help, range, calibration and backlight have a dedicated button
- **Supplied complete**
  - Each meter is supplied complete with sensor, calibration solution, beakers, PC software and connection cable, instruction manual, quick start guide and batteries in a rugged, custom carrying case.



### For Universal Applications

HI98192 is a waterproof, portable conductivity meter that has an expanded conductivity range from 0.000  $\mu\text{S}/\text{cm}$  to 400  $\text{mS}/\text{cm}$ , as well as TDS, resistivity and three salinity scales. This meter offers a quick connect four-ring probe and allows the user to adjust the nominal cell constant. HI98192 is also ready to perform all three stages of USP <645> method required for EC measurement of ultrapure water.



### Backlit Graphic LCD Display

The HI98192 features a backlit graphic LCD with on-screen help. The graphic display allows for the use of virtual keys to provide for an intuitive user interface.

### Waterproof Protection

The meter is enclosed in an IP67 rated waterproof casing and can withstand immersion in water at a depth of 1 m for up to 30 minutes. The probe features an IP68 rating for continuous immersion in water.



### Quick connect probe

The HI763133 four-ring platinum conductivity probe features a quick connect DIN connector to make attaching and removing the probe simple and easy.



### Calibration


Choose from seven memorized standards and obtain up to a five point conductivity calibration. For salinity (% range), HI7037 standard allows users to perform a one point calibration.

### USP <645>

HI98192 can be used to perform all three stages of USP method required for EC measurement of ultrapure water and generates a report when any of the three stages are met.



- Three stages of conformity
  - Performs all 3 stages of USP <645> water quality testing requirements



- On-screen guide
  - Users are provided with on-screen instructions for each USP stage



- Progress bar
  - Displays reading stability progress towards meeting stage 2 requirements



### Measurement

EC and TDS measurements are fully customizable and include: cell constant selection between 0.010 and 10.000, selection of linear or natural water (non-linear) or no temperature compensation (for actual conductivity reading), configurable temperature compensation coefficient range


from 0.00 to 10.00%/°C, choice of reference temperatures of 15°C, 20°C and 25°C, and a selectable TDS factor between 0.40 and 1.00.

Ten sets of customized measurement parameters can be stored as a user profile and later recalled.



### Data Logging

The HI98192's allows storage of up to 400 log-on-demand samples or 1000 lot logging samples that can be later transferred to a PC with the supplied HI920015 USB cable and HI92000 software.



### GLP

Comprehensive GLP functions are directly accessible by pressing the GLP key. Calibration data, including date, time and calibration values are stored for retrieval at a later time

### Intuitive Keypad

The fitted rubber keypad has dedicated keys for power, backlight, up/down arrows, help and alphanumeric characters. The meter also features two virtual soft keys that navigate the user through the configuration of each parameter, meter setup, and logging of data. The interface is intuitive for any user's level of experience.




### AutoHold

Pressing AutoHold during measurement will automatically hold the first stable reading on the display.

## Dedicated Help Key

Contextual help is always available through a dedicated "HELP" key. Clear tutorial messages and directions are available on-screen to quickly and easily guide users through setup and calibration. The help information displayed is relative to the setting/option being viewed.



## Setup screen

Our extensive setup screen features a host of configurable options such as time, date, temperature units and language for help screens and guides



## PC Connectivity

Logged data can be transferred to a Windows compatible PC with the included HI920015 micro USB cable and HI92000 software.

## Long Battery Life

The display of the meter has a battery icon indicator to show the remaining power. The meter uses four 1.5V AA batteries that provide up to 200 hours of battery life.



## Rugged custom carrying case

The HI98192 meter, probe, and all accessories are supplied in the HI720192 rugged carrying case designed to provide years of use. The inside compartment of the carrying case is thermoformed to securely hold and protect all of the components.

Specifications	HI98192	
EC	Range	0 to 400 mS/cm (shows values up to 1000 mS/cm actual conductivity)** 0.001 to 9.999 $\mu$ S/cm*; 10.00 to 99.99 $\mu$ S/cm; 100.0 to 999.9 $\mu$ S/cm; 1.000 to 9.999 mS/cm; 10.00 to 99.99 mS/cm; 100.0 to 1000.0 mS/cm (autoranging)
	Resolution	0.001 $\mu$ S/cm*; 0.01 $\mu$ S/cm; 0.1 $\mu$ S/cm; 0.001 mS/cm; 0.01 mS/cm; 0.1 mS/cm
	Accuracy	$\pm$ 1% of reading ( $\pm$ 0.01 $\mu$ S/cm or 1 digit, whichever is greater)
	Calibration	automatic up to five points with seven memorized standards (0.00 $\mu$ S/cm, 84.0 $\mu$ S/cm, 1.413 mS/cm, 5.00 mS/cm, 12.88 mS/cm, 80.0 mS/cm, 111.8 mS/cm)
TDS	Range	0.00 to 99.99 ppm; 100.0 to 999.9 ppm; 1.000 to 9.999 g/L; 10.00 to 99.99 g/L; 100.0 to 400.0 g/L (autoranging)
	Resolution	0.01 ppm; 0.1 ppm; 0.001 g/L; 0.01 g/L; 0.1 g/L
	Accuracy	$\pm$ 1% of reading ( $\pm$ 0.05 ppm or 1 digit, whichever is greater)
Resistivity	Range	1.0 to 99.9 $\Omega$ •cm; 100 to 999 $\Omega$ •cm; 1.00 to 9.99 K $\Omega$ •cm; 10.0 to 99.9 K $\Omega$ •cm; 100 to 999 K $\Omega$ •cm; 1.00 to 9.99 M $\Omega$ •cm; 10.0 to 100.0 M $\Omega$ •cm* (autoranging)
	Resolution	0.1 $\Omega$ •cm; 1 $\Omega$ •cm; 0.01 K $\Omega$ •cm; 0.1 K $\Omega$ •cm; 1 K $\Omega$ •cm; 0.01 M $\Omega$ •cm; 0.1 M $\Omega$ •cm*
	Accuracy	$\pm$ 1% of reading ( $\pm$ 10 $\Omega$ or 1 digit, whichever is greater)
Salinity	Range	% NaCl: 0.0 to 400.0%; practical salinity: 0.00 to 42.00 (PSU); seawater scale: 0.00 to 80.00 (ppt)
	Resolution	0.1%; 0.01
	Accuracy	$\pm$ 1% of reading
Temperature <sup>†</sup>	Calibration	max. one point only in % NaCl range with HI7037 standard; use conductivity calibration for all other ranges
	Range	-20.0 to 120.0°C; -4.0 to 248.0°F
	Resolution	0.1°C; 0.1°F
	Accuracy	$\pm$ 0.2°C; $\pm$ 0.4°F (excluding probe error)
Additional Specifications	Calibration	one or two points
	Cell Constant Setup	0.010 to 10.000
	Temperature Compensation	NoTC, linear (-20.0 to 120.0°C (-4.0 to 248.0°F)), non linear (0 to 36°C (32 to 98.6°F)) ISO/DIS 7888 std
	Reference Temperature	15°C, 20°C and 25°C
	Temperature Coefficient	0.00 to 10.00 %/°C
	TDS Factor	0.40 to 1.00
	Probe	HI763133 platinum, four-ring conductivity/TDS probe with internal temperature sensor and 1 m (3.3') cable (included)
	Logging	log-on-demand: 400 samples; lot logging: 5, 10, 30 sec, 1, 2, 5, 10, 15, 30, 60, 120, 180 min (max 1000 samples)
	Memorized Profiles	up to 10
	Measurement Modes	autorange, autoend, lock and fixed range
	PC Connectivity	opto-isolated sealed USB (with HI92000 software and micro USB cable)
	Battery Type / Life	1.5V AA batteries (4) / approximately 100 hours of continuous use (without backlight), 25 hours with backlight;
	Auto-off	user selectable: 5, 10, 30, 60 min, disabled
	Environment	0 to 50°C (32 to 122°F); RH 100% IP67
	Dimensions/Weight	185 x 93 x 35.2 mm (7.3 x 3.6 x 1.4") / 400 g (14.2 oz.)
Ordering Information	<b>HI98192</b> is supplied with HI763133 platinum, four-ring conductivity/TDS probe, HI7031M 1413 $\mu$ S/cm calibration solution (230 mL), HI7035 111.8 mS/cm calibration solution (230 mL), 100 mL plastic beaker (2), HI92000 PC software, HI920015 micro USB cable, 1.5V AA batteries (4), quick start guide, quality certificate and instruction manual in an HI720192 rugged carrying case with custom insert.	

\* The 0.000  $\mu$ S/cm EC range and 0.1 M $\Omega$ •cm resistivity range are not available with the optional 4m cable probe

\*\* Uncompensated temperature reading

(†) Reduced to actual sensor limits