

IBC station out of polyethylene (low density)



Order No.:

13054

Configuration

IBC station

- ✓ out of polyethylene (low density), blue
- ✓ with bearing block
- ✓ accessible by forklift, with trucklift pockets
- ✓ Dimensions (mm): 1380 x 1575 x 760

Technical Data

Width (external)	1,380 mm
Depth (external)	1,575 mm
Height (external)	760 mm
Weight	100 kg
Storage capacity	1 x 1000-L-IBC
Load capacity in kg/storage area	2,000 kg/storage area

load capacity in kg	2,000 kg
Sump capacity	1000 litres
ecl@ss 10.0	40-06-02-09
ecl@ss 9.1	40-06-02-03
ecl@ss 5.1.4	21-10-90-90
ecl@ss 11.0	40-06-02-09
ecl@ss 8.1	40-06-02-03

Adress

asecos GmbH

Safety and Environmental
Protection
Weiherfeldsiedlung 16-18 and
Leipziger Straße 41
63584 Gründau / Deutschland

Phone: +49 6051 9220-0

Fax: +49 6051 9220-10

configurator@asecos.com

The Company

contact
catalogues and brochures
newsletter
driving directions
imprint
privacy policy
gtc

When configuring a safety cabinet, please adhere to the applicable national rules and regulations for the storage of hazardous substances. If you are unsure, the asecos experts will be happy to help you further