

CL Series - Illuminators

CLD-01



CLD-01 with CL-11.1

Flexible and professional cold light illuminator with high power, extra-efficiency **14W LED** system, **extremely bright and uniform**.
Optical power: **1000 lumen**.
Brightness control potentiometer, external power supply.



Mechanical component
CLD-01 + CL-11.1

CLD-01 Accessories

The output can be coupled to the following accessories:

CL-11.1: Double-arm optical fiber guide with focusing lenses. Arm length 500 mm.

CL-17.1: Polarizing filters (pair) for CL-11.1.


CL-12: Ring optical fiber guide (length 700 mm).

Guide diameter 16 mm.

Diameter of the fixing ring: 55mm.

The circular end is suitable for all stereo series.

CL-11.1



Double-arm guide for CLD-01, with focusing lenses.

Arm length 500 mm. Each arm fitted with focusable lens adapter.

Illuminance (at 10 cm distance): **70.000 lux**.

Optional accessory:

CL-17: lens pair with built-in linear polarizer.



Ring optical fiber guide for CLD-01.

Length 700 mm, diameter 16 mm.

The circular end is suitable for all series, by using the three locking screws. Diameter of the fixing ring: 55mm.

Illuminance (at 10 cm distance): **40.000 lux**.