



*Digital binocular microscope with tablet,  
1000x, PLAN, multi-plug/EU*

<b>Observation Method - Transmitted Light</b>	Brightfield	Yes
	Simple polarized light	As optional

<b>Main Body</b>	Type	Upright
	Construction material	Aluminum die-cast
	Trasportation handle	Yes

<b>Head</b>	Type	Binocular (Siedentopf)
	Inclination	30°
	360° rotating	Yes
	Interpupillary distance (mm)	48-75
	Dioptric adjustment	On left tube
	Fixing screw for eyepieces	Yes
	Tube inner diameter (mm)	23

<b>Eyepieces</b>	Field number (mm)	18
	Magnification	10x
	Pointer	As optional
	Micrometric scale	As optional
	Diameter of micrometer glass (mm)	20
	High eyepoint (for glass wearers)	Yes

<b>Nosepiece</b>	Positions	Quadruple
	Reversed	Yes
	Bi-directional	Yes
	Rotation on ball bearings	Yes
	Objective thread	RMS

<b>Objectives</b>	Optical system	160
	Anti-fungus treatment	Yes
	Parfocal distance (mm)	45
	Standard magnifications	40x-1000x
	Type	N-PLAN
		4x/0.10, W.D. 15.2 mm
		10x/0.25, W.D. 5.5 mm
	40x/0.65, W.D. 0.45 mm	
	100x/1.25 (Oil/Water), W.D. 0.13 mm	

<b>Stage</b>	Type	Double layer
	Dimensions (mm)	125x115
	Moving mechanism	Rack and pinion
	Moving range (mm)	70x30
	Material	Anti-scratch painting
	Specimen holder	Yes
	Slide number	1
	X-Y movement	Yes
	X-Y Vernier scale	Yes
	Vernier scale accuracy (mm)	0.1

<b>Condenser - Single Position</b>	Type	Abbe
	Numerical aperture (N.A.)	1.25
	Centrable	Pre-centered
	Focusable	By rotation

<b>Focusing System</b>	Type	Coaxial coarse & fine
	Coarse total travel (mm)	18
	Fine total travel (per single rotation) (mm)	0,4
	Fine graduations	100
	Fine resolution ( $\mu\text{m}$ )	4
	Upper stop to prevent contact	Yes
	Adjustable tension	Yes

<b>Transmitted Illumination</b>	Type	X-LED
	X-LED type	X-LED2
	Light source power (W)	3
	Brightness control	Manual
	Lifetime (hours)	> 65,000
	Temperature (K)	6,300
	Max. required power (W)	6

<b>Power Supply for Transmitted Illumination</b>	Type	External
	Microscope connector	Jack, 2.1 mm
	Power plug type	Multi-plug (EU, UK, US)
	Input voltage	100/240 Vac, 50/60 Hz
	Output voltage	6 Vdc 2.5 A

<b>Accessories Included</b>	Dust cover	Yes
	Immersion oil (10ml)	Yes
	Tension adjustment tool	Yes
	User Manual	Digital version (downloadable)
	Calibration slide	Yes
	Touch pen	Yes
	USB cable (m)	0,5

<b>Additional Information</b>	External rechargeable battery pack (as optional). Tablet Keyboard (as optional).
-------------------------------	---

<b>Product Dimensions</b>	Height (mm)	525
	Width (mm)	260
	Depth (mm)	320

<b>Product Weight</b>	(kg)	7,4
-----------------------	------	-----

<b>Camera specifications</b>	PC Camera resolution (MP)	3.1
	Camera resolution (n° of pixels: W x H)	2048x1536
	USB Signal output	USB 2.0
	Color / Monochrome	Color
	Sensor Size	1/2.5"
	Sensor Technology	CMOS
	Sensor Type	APTINA CMOS
	Rolling Shutter	Yes
	Image Format	4/3
	Pixel Size (µm)	2.2x2.2
	Frame rate full resolution (fps)	8@1280x1024
	Frame rate other resolution (fps)	30@640x480
	Sensitivity	0.53 V/lux-second
	Signal/Noise Ratio (DB)	40.5
	Dynamic range (DB)	66.5
	ADC conversion	12 Bit
	Color Depth	8 Bit
	Exposure time	... - 1.5 sec
	Binning	1x1
	IR filter	Yes
IR filter range (nm)	680	
Camera Power	PC USB	
C-Mount	Yes	

<b>Camera accessories</b>	Calibration slide	Yes
---------------------------	-------------------	-----

<b>Environment specifications</b>	Working Temperature	-10°C up to +50°C
	Storage Temperature	-20°C up to +60°C
	Relative Humidity	30% to 80%
	Storage Humidity	10% to 60%

<b>Operating System</b>	OS	Windows 10 (64Bit)
-------------------------	----	--------------------

<b>Available Software</b>	SW	PROVIEW
---------------------------	----	---------

<b>Warranty</b>	Years	2
-----------------	-------	---

<b>Tablet</b>	Operating system	Windows 10 (64Bit)
	CPU	Intel® Celeron, N3350
	CPU speed	1.10 GHz
	Graphic card	Intel® HD Graphics 500
	RAM	Ram 6 GB DDR3
	Display size	LED 10.1" IPS Multi Touch Screen
	Display resolution	1920x1200
	Storage	Hdd 64 GB
	Network	802.11b/g/n/ac,2.4GHz+5.0GHz
	Input ports	USB 3.0, Type C, Micro SD card reader, Microphone, DC in
	Output ports	Headphone - Micro HDMI
	Battery Type	Lithium-ion
	Battery capacity	3500 mAh
	Power consumption	24.05W
	Power supply	12V 2A EU / US
	Dimensions (mm)	247 x 165 X 9
Weight (Kg)	0.57	
Language	Multilanguage	

<b>Tablet accessories</b>	USB cable USB-B to USB-A (0.5m)	Yes
	Touch pen	Yes

DOMINIQUE DUTSCHER SAS