



High Performance USB 3.0 C-mount
Microscope Camera

General specifications	USB output	Yes
	C-Mount	Yes
	Dimensions (mm)	68 x 68 x 46
	Weight (kg)	0.265

Sensor	Camera resolution (n° of pixels: W x H)	3072x2048
	Color / Monochrome	Color
	Sensor Size	1/1.8"
	Sensor Technology	CMOS
	Sensor Type	SONY EXMOR
	Image Format	3/2
	Pixel Size (mm)	2.4x2.4
	Acquisition technology	Rolling shutter
	Dynamic range (DB)	66.8
	G sensitivity	425mV at 1/30s
	Dark Signal	0.15mV at 1/30s
	ADC conversion	8 Bit - 12Bit
	Color Depth	1, 4, 8, 24 Bit
	Exposure time	0.1 msec - 15 sec
	Binning	1x1; 2x2
	IR filter	Yes
IR filter range (nm)**	380-650 (IR CUT)	

** If used for red emission fluorescence wavelengths above 650nm please order it by specifying with "AR GLASS"

USB	PC Camera resolution (MP)	6.3
	USB standard	USB3.0
	Frame rate full resolution (fps)	30@3072x2048
	Frame rate other resolution (fps)	38@1536x1024

Camera Power Supply	Connector	USB
	Output voltage	PC USB

Camera accessories	Calibration slide	Yes
	USB cable (1.8m)	Yes

Environment	Working Temperature	-10°C up to +50°C
	Storage Temperature	-20°C up to +60°C
	Relative Humidity	30% to 80%
	Storage Humidity	10% to 60%
Operating System	OS	Windows 7
	OS	Windows 8
	OS	Windows 10 (32Bit)
	OS	Windows 10 (64Bit)
	OS	Windows 11
	OS	Osx (MAC Osx) starting from 10.7.5
	OS	Linux
Available Software	PC SW	PROVIEW
	PC SW	LITEVIEW
PC requirements	PC	CPU: Intel Core2 - 2.8GHz or higher
	PC	RAM: 2GB or more
	PC	USB 3.0

DOMINIQUE DUTSCHER SAS