

FICHE TECHNIQUE

Référence	679664
Désignation	Corning® 5 x 7 Inch Top PC-410D Stirrer with Digital Display



Description :

- ✓ 2 year warranty
- ✓ This product is CE marked and UL/cUL approved
- ✓ Exclusive closed-loop stirring control monitors and regulates the stirring speed from 60-1150 RPM for aqueous, viscous, or semi-solid solutions.
- ✓ Stronger, larger magnet improves stir bar coupling combined with automatic ramp up speed adjustment minimizes decoupling.
- ✓ Two piece casting design deflects spills away from electronics and includes a built in mount for an optional 18 (45.7cm) support rod (Cat. No. 440129)
- ✓ Number of Stirring Positions 1
- ✓ Top Size 5 x 7 inches
- ✓ Power 230V, 50Hz
- ✓ Amperage 73
- ✓ Watts 0,4
- ✓ Stir Range 60 - 1150 rpm

Unité de vente :

1 unité