

ClearLine AlumaSeal II sealing films

Application :


PCR, long-term storage

Advantage :


Don't roll back on itself

Compatible with :

Two component plate -Skirted and semi-skirted


Features

Packaging	Films
End-tabs	Features two end-tabs with perforations
Collar	Without collar
Material	Aluminium
Adhesive material	Acrylic
Piercable	Yes
Chemically resistant	Yes
Breathable	No
Opacity	Light blocking
Colour	-
Sterile	No - DNase RNase free
Functional temperature range	-80°C to +120°C
Film/Foil thickness	35,6 µm
Adhesive thickness	27,9 µm
Dimensions (without end-tabs)	125,4 x 82,6


Units : 100 films