

ClearLine Zone-Free sealing films

Application :


HPLC, Sonication

Advantage :


Adhesive-free zones on center to facilitate use pipet tips or robotic probes

Compatible with :

Skirted and semi-skirted


Features

Packaging	Films
End-tabs	Features two end-tabs with perforations
Collar	Without collar
Material	Polyethylene
Adhesive material	Acrylic
Piercable	Yes
Chemically resistant	No
Breathable	No
Opacity	Transparent
Colour	-
Sterile	No
Functional temperature range	-40°C to +90°C
Film/Foil thickness	69,9 µm
Adhesive thickness	26,7 µm
Dimensions (without end-tabs)	121,9 x 79,4


Units : 50 films