

## ClearLine SealPlate sealing films

**Application :**


Short-Term Storage, Incubation, ELISA

**Advantage :**


Minimizes evaporation, available with color dot

**Compatible with :**

Skirted and semi-skirted


**Features**

<b>Packaging</b>	Films
<b>End-tabs</b>	Features two end-tabs with perforations
<b>Collar</b>	Without collar
<b>Material</b>	Polyester
<b>Adhesive material</b>	Acrylic
<b>Piercable</b>	No
<b>Chemically resistant</b>	No
<b>Breathable</b>	No
<b>Opacity</b>	Transparent
<b>Colour</b>	Assorted (green, lavender, orange, red and blue)
<b>Sterile</b>	No
<b>Functional temperature range</b>	-40°C to +120°C
<b>Film/Foil thickness</b>	50,8 µm
<b>Adhesive thickness</b>	26,7 µm
<b>Dimensions (without end-tabs)</b>	125 x 79,4


**Units : 5 x 10 films**

