

ClearLine ThermalSeal A sealing films

Application :

PCR

Advantage :


Extra-strong adhesive to minimize evaporation

Compatible with :

All kind of skirts


Features

Packaging	Films
End-tabs	Features two end-tabs with perforations
Collar	With collar
Material	Polyester
Adhesive material	Acrylic
Piercable	No
Chemically resistant	No
Breathable	No
Opacity	Transparent
Colour	-
Sterile	No - DNase RNase free
Functional temperature range	-40°C to +120°C
Film/Foil thickness	50,8 µm
Adhesive thickness	41,9 µm
Dimensions (without end-tabs)	118,1 x 78,3


Units : 100 films