

ClearLine AlumaSeal 96 sealing films

Application :


PCR, long-term storage

Advantage :


Reinforced sealing for 96-wells plate

Compatible with :

All kind of skirts


Features

Packaging	Films
End-tabs	Features one end-tabs with perforations
Collar	With collar
Material	Aluminium
Adhesive material	Acrylic
Piercable	Yes
Chemically resistant	No
Breathable	No
Opacity	Light blocking
Colour	-
Sterile	No - DNase RNase free
Functional temperature range	-80°C to +120°C
Film/Foil thickness	38,1 µm
Adhesive thickness	37,6 µm
Dimensions (without end-tabs)	117,5 x 77,8


Units : 100 films