

ClearLine AlumaSeal 384 sealing films

Application :


PCR, long-term storage

Advantage :


Reinforced sealing for 384-wells plate

Compatible with :

Skirted and semi-skirted


Features

Packaging	Films
End-tabs	Features one end-tabs with perforations
Collar	Without collar
Material	Aluminium
Adhesive material	Acrylic
Piercable	Yes
Chemically resistant	No
Breathable	No
Opacity	Light blocking
Colour	-
Sterile	No - DNase RNase free
Functional temperature range	-80°C to +120°C
Film/Foil thickness	38,1 µm
Adhesive thickness	37,6 µm
Dimensions (without end-tabs)	123,8 x 82,6


Units : 100 films