

ClearLine X-Pierce sealing films

Application :


HPLC, Sonication

Advantage :


After sampling and removing the tip, the "X" closes and the sample is still protected from contamination

Compatible with :

Skirted and semi-skirted


Features

Packaging	Films
End-tabs	Features two end-tabs with perforations
Collar	Without collar
Material	Vinyle
Adhesive material	Acrylic
Piercable	Yes
Chemically resistant	No
Breathable	No
Opacity	Transparent
Colour	-
Sterile	Yes
Functional temperature range	-40°C to +90°C
Film/Foil thickness	88,9 µm
Adhesive thickness	17,8 µm
Dimensions (without end-tabs)	124,5 x 79,4


Units : 50 films