

ClearLine AbsorbMax sealing films

Application :


Fluorescence, luminescence

Advantage :


Absorbs stray light, reducing the background

Compatible with :

Skirted and semi-skirted


Features

Packaging	Films
End-tabs	Without end-tabs
Collar	Without collar
Material	Vinyle
Adhesive material	Acrylic
Piercable	No
Chemically resistant	No
Breathable	No
Opacity	Light blocking
Colour	-
Sterile	No
Functional temperature range	-40°C to +80°C
Film/Foil thickness	203,2 µm
Adhesive thickness	36,8 µm
Dimensions (without end-tabs)	114,3 x 76,2


Units : 50 films