

### ClearLine BrightMax sealing films

**Application :**


Fluorescence, luminescence

**Advantage :**


Reflects light and increases sensitivity

**Compatible with :**

Skirted and semi-skirted


**Features**

Packaging	Films
End-tabs	Without end-tabs
Collar	Without collar
Material	Vinyle
Adhesive material	Acrylic
Piercable	No
Chemically resistant	No
Breathable	No
Opacity	Light blocking
Colour	-
Sterile	No
Functional temperature range	-40°C to +80°C
Film/Foil thickness	203,2 µm
Adhesive thickness	36,8 µm
Dimensions (without end-tabs)	116,1 x 76,2


**Units : 50 films**