

ClearLine EZ-Pierce sealing films

Application :


HPLC, Sonication

Advantage :

Ideal for robotic systems

Compatible with :

Skirted and semi-skirted

**Features**

Packaging	Films
End-tabs	Features two end-tabs with perforations
Collar	Without collar
Material	Polyethylene
Adhesive material	Acrylic
Piercable	Yes
Chemically resistant	Yes
Breathable	No
Opacity	Transparent
Colour	-
Sterile	Yes
Functional temperature range	-40°C to +90°C
Film/Foil thickness	70 µm
Adhesive thickness	25 µm
Dimensions (without end-tabs)	142,9 x 82,6

Units : 50 films