


# Tubes



It is not recommended that these tubes be exposed to temperatures above 60°C.

## Gas delivery tubes, polypropylene



- Pre-bent rigid polypropylene delivery tubes
- Unbreakable in normal use - ideal substitutes for fragile glass alternatives
- Suitable for many types of gas collection experiments in schools and universities

| Product Code | Key | Type                           | Tube O.D. (mm) | Tube I.D. (mm) | Pack qty. |
|--------------|-----|--------------------------------|----------------|----------------|-----------|
| DT001        | A   | 90 Degree                      | 6              | 4              | 5         |
| DT002        | B   | Bung Top                       | 6              | 4              | 5         |
| DT003        | C   | Side Arm                       | 6              | 4              | 5         |
| DT004        | D   | Straight tube                  | 6              | 4              | 5         |
| DT005        | E   | Double Bend                    | 6              | 4              | 5         |
| DT006        | F   | U Bend                         | 6              | 4              | 5         |
| DT007        | G   | Large U Bend                   | 6              | 4              | 5         |
| DT008        | H   | Small U bend                   | 6              | 4              | 5         |
| DT009        | I   | Test tube side arm             | 6              | 4              | 5         |
| DT001MP      | -   | Multi pack - One of each shape | 6              | 4              | 9         |



## Tubes, test, with rim, medium wall

**PYREX®**

- Conforms to ISO 4142
- High quality test tubes designed and constructed for optimum performance
- Manufactured from Pyrex® borosilicate glass which gives superior performance to neutral borosilicate and soda-lime glass
  - Allows use at temperatures up to 500°C
  - Excellent resistance to chemical attack

| Product Code | Approx capacity to rim (ml) | Dimensions O.D. x length (mm) | Wall thickness (mm) | Pack qty. |
|--------------|-----------------------------|-------------------------------|---------------------|-----------|
| 1620/02M     | 4                           | 10 x 75                       | 1.0                 | 100       |
| 1620/04M     | 6                           | 12 x 75                       | 1.0                 | 100       |
| 1620/06M     | 8                           | 12 x 100                      | 1.0                 | 100       |
| 1620/09M     | 14                          | 16 x 100                      | 1.2                 | 100       |
| 1620/10M     | 18                          | 16 x 125                      | 1.2                 | 100       |
| 1620/12M     | 22                          | 16 x 150                      | 1.2                 | 100       |
| 1620/14M     | 23                          | 16 x 160                      | 1.2                 | 100       |
| 1620/15M     | 34                          | 18 x 180                      | 1.2                 | 100       |
| 1620/16M     | 28                          | 18 x 150                      | 1.2                 | 100       |
| 1620/20M     | 50                          | 24 x 150                      | 1.2                 | 100       |
| 1620/22M     | 66                          | 24 x 200                      | 1.2                 | 50        |