

# Funnels



## Funnels, separating, conical, Rotaflor<sup>®</sup> stopcock



- Complies with ISO 4800, Type 1
- Manufactured from borosilicate glass
- With GP Rotaflor<sup>®</sup> PTFE stopcock:
  - No lubrication required
  - No contaminating greases
  - No seizure

Product Code	Nom. capacity (ml)	Stopcock bore (mm)	Socket size	Stopcock	Pack qty.
D91/100	100	3.0	14/23	GP3K	1
D92/100	100	3.0	19/26	GP3K	1
D93/250	250	3.0	24/29	GP3K	1
D93/500	250	6.0	24/29	GP6K	1



## Funnels, separating, pear-shape, glass key

**PYREX<sup>®</sup>**

- Complies with ISO 4800, Type 2
- Manufactured from Pyrex<sup>®</sup> glass for corrosion-free performance
- With interchangeable glass key
- Supplied with glass stopper

Product Code	Nom. capacity (ml)	Stopcock bore (mm)	Stopper size	Stopcock	Pack qty.
2180/02M	50	2.0	19/26	SSD102K	1
2180/04M	100	2.0	19/26	SSD102K	1
2180/06M	250	2.5	24/29	SSD103K	1
2180/08M	500	4.0	24/29	2392/24	1
2180/10M	1000	4.0	29/32	2392/24	1
2180/12M	2000	6.0	29/32	SSD106K	1
2180/14M	5000	6.0	34/35	SSD106K	1



5L size supplementary to ISO range.