

ClearLine SealPlate sealing films

Application :


Short-Term Storage, Incubation, ELISA

Advantage :


Minimizes evaporation, available with color dot

Compatible with :

Skirted and semi-skirted


Features

Packaging	Roll
End-tabs	Features two end-tabs with perforations
Collar	Without collar
Material	Polyester
Adhesive material	Acrylic
Piercable	No
Chemically resistant	No
Breathable	No
Opacity	Transparent
Colour	Natural
Sterile	Yes
Functional temperature range	-40°C to +120°C
Film/Foil thickness	38,1 µm
Adhesive thickness	26,7 µm
Dimensions (without end-tabs)	120,7 x 79,4



Units : Starter kit with SealMate dispenser and 2 rolls of 100 films