

ClearLine ThermalSeal 2 sealing films

Application :


PCR

Advantage :


Extra-strong adhesive to minimize evaporation

Compatible with :

Skirted and semi-skirted


Features

Packaging	Films
End-tabs	Features two end-tabs with perforations
Collar	Without collar
Material	Polyester
Adhesive material	Acrylic
Piercable	No
Chemically resistant	No
Breathable	No
Opacity	Transparent
Colour	-
Sterile	No - DNase RNase free
Functional temperature range	-40°C to +120°C
Film/Foil thickness	50,8 µm
Adhesive thickness	41,9 µm
Dimensions (without end-tabs)	125,1 x 79,4


Units : 100 films