

ClearLine eXtreme FoilSeal sealing films

Application :


PCR

Advantage :


Excellent chemical resistance

Compatible with :

All kind of skirts


Features

Packaging	Roll
End-tabs	Features two end-tabs with perforations
Collar	With or without collar
Material	Aluminium
Adhesive material	Acrylic
Piercable	Yes
Chemically resistant	No
Breathable	No
Opacity	Light blocking
Colour	-
Sterile	No - DNase RNase free
Functional temperature range	-20°C to +120°C
Film/Foil thickness	50,8 µm
Adhesive thickness	36,8 µm
Dimensions (without end-tabs)	117,1 x 78,3


Units : 1 roll of 500 films