

**Bellco Glass, Inc.
Specification Sheet
Product #: 7744-20220**

Description: The Bellco Bench Top Orbital Shakers are ideal for staining and washing electrophoresis gels or for any other applications requiring mixing or agitation of solutions. They are engineered to operate between the limits of 10 and 350 rpm, and to hold their speed at any selected setting to plus or minus five percent.

Load: 11kg max.
Speed Range: 0-350 RPM
Dimensions without tray: 28 x 28 x 13 cm
Circular Orbit: 2.5cm
Electrical Rating: 230 VAC fused at 0.5 Amp

Features:

Cast iron ballast eliminates walking of unit.
Peg and Grommet platform design permits quick tray changes
Accommodates a variety of flasks, beakers, slides, tubes, etc
Platform travel is ½” offset to give one inch circular orbit
Ideal for hybridization and gel agitation

Tray:

Material: Painted Aluminum
Dimensions: 51 x 51 x 1.3cm

Use of this equipment is limited to conventional laboratory applications. It is not intended for use in adverse environments outside the environmental conditions listed below. It is also not intended for use with corrosive or explosive solutions.
Environmental Conditions, operating: indoor use, pollution degree 2, 4° to 50° relative humidity 0-90% non-condensing
Environmental Conditions, non-operating: -10° to 60° C, relative humidity 95% maximum

The information contained in this specification sheet we believe is correct to the best of our knowledge. The recommendations and suggestions herein are made without guarantee or representation as to results. We recommend that adequate tests be made in your laboratory or plant to determine if this product meets all of your requirements.



BELCO GLASS, INC.



Bellco Glass, Inc. · 340 Edrudo Road · Vineland, NJ · 08360
Ver: 7/05