



PRACTICAL INNOVATION

Ziath

DataPaq™ Linear Rack Scanner Version 2

2-year guarantee as standard

The Ziath Linear Rack Scanner Version 2 is for use with the DataPaq™ Express, Deep Focus, High Speed and Multi-Rack Scanners. It is simply attached to the scanner using a bracket with a magnetic place holder. No assembly of the linear scanner is required.



Features

- Use with Ziath DataPaq™ 2D barcode rack scanners
- Very quick and easy to install. No assembly required.
- Scans in milliseconds
- Wide range of placement options
- Quick & easy installation, no dongles required
- USB connection
- Operating systems: Windows XP, Vista, 7
- Attaches to the rack scanner using bracket with magnetic place holder
- Dimensions : 67 x 48 x 19mm (WxHxD)
- Durable construction - 2 year guarantee
- Free software upgrades for life
- Ziath's expertise and support come as standard



DataPaq™ Linear Rack Scanner Version 2

PRACTICAL INNOVATION

Easy Set-Up and Easy To Use

The DataPaq™ Linear Rack Barcode Scanner is very simple to attach to existing 2D scanners, and offers easy installation. It can be attached to any side of the DataPaq™ scanners using a bracket with a magnetic pad.

Our DataPaq™ software makes it simple to export the linear (rack) barcode data and the

tube data to Excel, XML, JSON or text and scanned images can also be saved.

The linear rack scan takes less than one second and the scanner is powered and controlled by USB cable, so needs no additional power cables.

The Deep Focus Linear Rack Scanner installed on the Deep Focus 2D barcode scanner



Ordering Information

Code	Description	Quantity
ZTS-1DR2-A6	DataPaq™ High Speed Linear Rack Scanner Version 2	1
ZTS-1DR2-AV6	DataPaq™ Deep Focus Linear Rack Scanner Version 2	1
ZTS-1DR2-EXP	DataPaq™ Express Linear Rack Scanner Version 2	1
ZTS-1DR2-A4	DataPaq™ Multi-Rack Linear Rack Scanner Version 2	1