

Block for 24 x 1,5 ml tapered

(Article number. 800011000)

for 1.5 ml Eppis

Key benefits:

1. Safety: All blocks are autoclavable
2. Stability: Strong block construction
3. Plug and Play: simple and fast exchanging - blocks suitable for all types of devices
4. Various applications: Accessories like Insulating top, Anti-condensation-plate and much more

Photos



Technical Details

Technical Data

BM 15 (Art. 800011000)

Dimension metal block

128,5 x 85,5 x 37,5 mm

Dimension plastic insulation

145 x 102 x 50 mm

Tubes

1,5 ml

Number of drillings

24

Drilling diameter	11 mm
Depth of drillings	36 mm
Shape of drillings	tapered
Weight	0,7 kg

Accessories

Suitable accessories for this block:

1. Anti-condensation plate: Art.-no. 800012900
2. Insulating lid: Art.-no. 800012800
3. Heating top: Art.-no. 800012500 (only cooling devices)
4. Assembly rack: Art.-no. 800014300