

EU Declaration of Conformity

| | | | |
|---------------|--|--------------------|--|
| Product: | Laboratory Equipment | File Reference: | TFR928051_003 |
| Manufacturer: | Cole-Parmer Ltd Beacon Road Stone, Staffordshire ST15 0SA United Kingdom | EU Representative: | Cole-Parmer Limited Bâtiment le Deltaparc Icade Paris Nord 2 7 rue du Canal BP 55437 Villepinte 95944 ROISSY Charles de Gaulle, France |

This declaration of conformity is issued under the sole responsibility of the manufacturer

Object of Declaration **Cole-Parmer Hotplates, Stirrers and Hotplate/Stirrers, 04806 series**

The object of the declaration described above is in conformity with the relevant Union Harmonisation Legislation

| | |
|--|-------------------|
| Electromagnetic Compatibility Directive | 2014/30/EU |
| Low Voltage Directive | 2014/35/EU |
| RoHS Directive | 2011/65/EU |

References to the relevant harmonised standards used or references to the other technical specifications in relation to which conformity is declared:

| | |
|--|--|
| IEC / EN 61326:2013 | Electrical equipment for the measurement, control and Laboratory use – Part 1: General requirements |
| IEC / EN 61010-1:2010 | Safety requirements for electrical equipment for measurement, control and laboratory use – Part 1: General requirements |
| IEC / EN 61010-2-010:2014 (Not applicable to stir-only models) | Safety requirements for electrical equipment for measurement, control and laboratory use – Part 2-010: Particular requirements for laboratory equipment for the heating of materials |
| IEC / EN 61010-2-051:2015 (Applicable to models with mixing functionality only) | Safety requirements for electrical equipment for measurement, control and laboratory use – Part 2-051: Particular requirements for laboratory equipment for mixing and stirring |

Signed for and on behalf of the above manufacturer

| | |
|---------------------------|--------------------|
| Year of Marking | 2019 |
| Place of Issue | Stone, UK |
| Authorised Representative | Neil Pomeroy |
| Title | Technical Director |

Signature



Date

15/10/2019

| Catalogue Number | Model | Description |
|------------------|----------------|---|
| 04806-24 | HP-300-BS-120 | Hotplate, aluminium, digital, blue, 120 V a.c. |
| 04806-25 | HP-300-BS | Hotplate, aluminium, digital, blue, 230 V a.c. |
| 04806-26 | HP-300-WS-120 | Hotplate, aluminium, digital, white, 120 V a.c. |
| 04806-27 | HP-300-WS | Hotplate, aluminium, digital, white, 230 V a.c. |
| 04806-30 | HP-300-BC-120 | Hotplate, ceramic, digital, blue, 120 V a.c. |
| 04806-31 | HP-300-BC | Hotplate, ceramic, digital, blue, 230 V a.c. |
| 04806-32 | HP-300-WC-120 | Hotplate, ceramic, digital, white, 120 V a.c. |
| 04806-33 | HP-300-WC | Hotplate, ceramic, digital, white, 230 V a.c. |
| 04806-36 | SHP-300-BS-120 | Hotplate stirrer, aluminium, digital, blue, 120 V a.c. |
| 04806-37 | SHP-300-BS | Hotplate stirrer, aluminium, digital, blue, 230 V a.c. |
| 04806-38 | SHP-300-WS-120 | Hotplate stirrer, aluminium, digital, white, 120 V a.c. |
| 04806-39 | SHP-300-WS | Hotplate stirrer, aluminium, digital, white, 230 V a.c. |
| 04806-42 | SHP-300-BC-120 | Hotplate stirrer, ceramic, digital, blue, 120 V a.c. |
| 04806-43 | SHP-300-BC | Hotplate stirrer, ceramic, digital, blue, 230 V a.c. |
| 04806-44 | SHP-300-WC-120 | Hotplate stirrer, ceramic, digital, white, 120 V a.c. |
| 04806-45 | SHP-300-WC | Hotplate stirrer, ceramic, digital, white, 230 V a.c. |
| 04806-48 | HP-400-B-120 | Premium hotplate, aluminium, blue, 120 V a.c. |
| 04806-49 | HP-400-B | Premium hotplate, aluminium, blue, 230 V a.c. |
| 04806-50 | HP-400-W-120 | Premium hotplate, aluminium, white, 120 V a.c. |
| 04806-51 | HP-400-W | Premium hotplate, aluminium, white, 230 V a.c. |
| 04806-64 | SHP-400-BS-120 | Premium hotplate stirrer, aluminium, blue, 120 V a.c. |
| 04806-65 | SHP-400-BS | Premium hotplate stirrer, aluminium, blue, 230 V a.c. |
| 04806-66 | SHP-400-WS-120 | Premium hotplate stirrer, aluminium, white, 120 V a.c. |
| 04806-67 | SHP-400-WS | Premium hotplate stirrer, aluminium, white, 230 V a.c. |
| 04806-80 | SHP-400-BC-120 | Premium hotplate stirrer, ceramic, blue, 120 V a.c. |
| 04806-81 | SHP-400-BC | Premium hotplate stirrer, ceramic, blue, 230 V a.c. |
| 04806-82 | SHP-400-WC-120 | Premium hotplate stirrer, ceramic, white, 120 V a.c. |
| 04806-83 | SHP-400-WC | Premium hotplate stirrer, ceramic, white, 230 V a.c. |