

## 15 Liter Heated Circulator



SD15H170

### Key Specifications

Description	170, 15 L Htg. Circulator
Controller Type	Standard Digital
Display	3.75" Touch-Pad LCD
Connectivity	RS232
Languages Supported	English
Swivel 180 Rotating Controller	Yes
Working Temperature Range °C	Ambient +10° to 170°
Temperature Stability °C	±0.04°
Fluid Optimization/Specific Heat Tuning	Automatic
Temperature Calibration Capability	1-point
Working Access (L x W x D) (cm)	21.2 x 27.6 x 14 cm
Pump Type	Pressure
Flammability Class (DIN 12876-1)	I (NFL)

## Key Features

Standard Digital Controller

### Key Features

- Large, universal icon and English display
- Swivel 180™ Rotating Controller
- On-board connectivity: RS-232 serial output
- On-screen prompts
- Automatic performance optimization
- Single-point calibration capability

## Common Specifications

Working Temperature Range °F	Ambient + 20° to 338°
Working Temperature Range °C	Ambient +10° to 170°
Reservoir Capacity (gallons)	3.96
Reservoir Capacity (liters)	15
Reservoir/Tank Material	Stainless Steel
Reservoir Cover	Included
DuraTop	Yes
LidDock	Yes
Working Access (L x W x D) (inches)	8.35 x 10.88 x 5.5 in
Working Access (L x W x D) (cm)	21.2 x 27.6 x 14 cm
Temperature Stability °F	±0.08°
Temperature Stability °C	±0.04°
Display	3.75" Touch-Pad LCD
Display Resolution (Set)	0.1
Display Resolution (Read)	0.1
Pump Type	Pressure
Pump Speed	Two
Process Connections	1/4" (F) NPT
Flammability Class (DIN 12876-1)	I (NFL)
Over-Temperature Protection / Failsafe Heater Control	Yes
Low Liquid Level Protection	Yes
Reservoir Drain	Yes
Cooling Coil	Yes

Maximum Ambient Temperature °F	95°
Maximum Ambient Temperature °C	35°
Overall Dimensions (L x W x H) (inches)	22.4 x 14.5 x 16.6 in
Overall Dimensions (L x W x H) (cm)	56.9 x 36.8 x 42.2 cm
Environmental Compliance	RoHS, WEEE
Shipping Weight (pounds)	62.0
Shipping Weight (kilograms)	28.1
Catalog Page Number	58-59

### 60 Hz Only

Part Number	SD15H170-A11B
Maximum Pressure (psi)	3.5
Maximum Pressure (bar)	0.24
Maximum Pressure Flow Rate (gpm)	2.90
Maximum Pressure Flow Rate (l/min)	11.0
Included Hardware	Nylon hose adapters for 3/8", 1/4", and 3/16"
Heater Wattage	1100
Electrical Requirements (VAC/Hz/Ph/A)	120/60/1/10
Regulatory Approvals	ETL

### 50 Hz Only

Part Number	SD15H170-A12E
Maximum Pressure (psi)	2.9
Maximum Pressure (bar)	0.20
Maximum Pressure Flow Rate (gpm)	2.70
Maximum Pressure Flow Rate (l/min)	10.2
Included Hardware	Nylon hose adapters for 3/8", 1/4", and 3/16", and 1/4" NPT to M16 adapter
Heater Wattage	2200
Electrical Requirements (VAC/Hz/Ph/A)	240/50/1/10
Regulatory Approvals	CE