

DispensMate

Bottle-Top Dispenser

Easy-to-use volume adjustment

Smooth piston design provides effortless dispensing

Adapters allow fitting to most common bottles

Filling tube adjusts easily for different size bottles

closure cap protects against reagent contact, easy to open/close without taking gloves off.



Features

- Excellent chemical resistance, high strength components made of PTFE, FEP, BSG, PP
- Fully autoclavable at 121°C (Liquid accessible parts)
- Available in 4 sizes for dispensing volumes from 0.5mL to 50mL
- Easy for cleaning and maintenance
- The optional variable discharge tube with safety handle allows a fast and precise dispensing
- Vapor pressure max: 500mbar; viscosity max; 500mm²/s; temperature max: 40°C; density max: 2.2g/cm³
- Supplied with most common adapters (S40, GL32, GL38, GL25, GL28)

Specifications

Cat. No.	Volume Range mL	Graduation mL	A _±		CV _≤	
			%	µL	%	µL
7032100001	0.5-5	0.1	0.5	25	0.2	10
7032100002	1.0-10	0.2	0.5	50	0.2	20
7032100003	2.5-25	0.5	0.5	125	0.2	50
7032100004	5.0-50	1.0	0.5	250	0.2	100

Accessories

Cat. No.

Description

17100553

GL45, Adapter, 45mm

17000069

S40, Adapter, 45/40mm

17400131

GL32, Adapter, 45/32mm

17400132

GL38, Adapter, 45/38mm

17400133

GL25, Adapter, 32/25mm

17400134

GL28, Adapter, 32/28mm

17400037

Reagent Bottle (Brown, 1L, Optional)

17400021

Filling tube(m)

17100073

Discharge tube(m)