

## TECHNICAL DATA SHEET

---

<b>Référence</b>	861141
<b>Désignation</b>	Overhead Stirrer



---

### Description :

- ✓ High reliability and outstanding performance
- ✓ A wide range of speed from 50 to 2200rpm
- ✓ Brushless DC motor for long life, maintenance free and explosion proof
- ✓ LED screen for monitoring actual speed
- ✓ Safety circuits allow for safe stop function in anti-stall or overload conditions
- ✓ Max. stirring quantity(H<sub>2</sub>O) : 20L
- ✓ Motor type : brushless DC motor
- ✓ Motor input power : 60W
- ✓ Motor output power : 50W
- ✓ Voltage : 100-240V, 50/60 Hz
- ✓ Power : 70W
- ✓ Speed range : 50-2200rpm
- ✓ Speed display accuracy : ±3rpm
- ✓ Speed display : LED
- ✓ Overload protection display : LED lights
- ✓ Max. torque: 40Ncm
- ✓ Viscosity max. : 10000mPas
- ✓ Chuck range diameter : 0.5-10mm
- ✓ Dimension[WxHxD] : 83x220x186mm
- ✓ Weight : 2.8kg
- ✓ Protection class : IP42
- ✓ Permissible ambient temperature and humidity : 5-40°C, 80%RH

### Units:

1 Unit

---