

GeneTouch Thermal Cycler

Flexibility is a core element of the GeneTouch PCR system. Offering not less than five different types of interchangeable blocks, the GeneTouch chassis and block design provides you with plenty of options. On the basis of the established GenePro, GeneTouch has a convenient and clear touch-screen display.

- User-friendly and intuitive software
- 6.5" color touch-screen for convenient usage
- Auto-recognition of the inserted block
- 96-well and 384-well blocks with gradient with up to 30°C temperature range
- Adjustable hot lid pressure
- 5 interchangeable blocks available



GeneTouch Specifications

| Name | GeneTouch | | | | |
|--------------------------------------|--|------------------------------------|------------------------------|--|---------------------------|
| Model/ Cat. No. | TC-EA(Main Body) BYQ607101E | | | | |
| Block Model Cat. No. | B-96GA BYQ607102E | B-3048UA BYQ607106E | B-384GA BYQ607103E | B-48DA BYQ607103E | B-41A BYQ607105E |
| Sample Capacity | 96-PCR Plate (full-skirted) 96×0.2ml tubes 12×8-strip | 30×0.5ml 48×0.2ml 4×12-strip | 384-PCR plate (full skirted) | 48×0.2ml tubes 6×8-strip each block | 4×standard in situ plates |
| Cooling Technology | Peltier-Based | | | | |
| Display | 6.5 inch, 262, 144 Color LCD Display and Touch Screen | | | | |
| Temp. Range | 4°C~105°C | | | | |
| Heating Speed of Ramping | Up to 4°C/sec | Up to 2.8°C/sec | Up to 2.8°C/sec | Up to 4°C/sec | Up to 1.8°C/sec |
| Cooling Speed of Ramping | Up to 4°C/sec | Up to 2.8°C/sec | Up to 2.8°C/sec | Up to 4°C/sec | Up to 1.8°C/sec |
| Temp. Uniformity | ≤±0.2°C | | | | |
| Temp. Accuracy | ≤±0.1°C (55°C) ≤±0.2°C (≥90°C) | | | | |
| Temp. Control Mode | Block or Tube | | | | |
| Ramping Range Adjustable | 0.1-4°C | | | | |
| Memory | ≥250 Typical Programs Onboard, Unlimited with USB Drive Expansion | | | | |
| Max. No. of Cycles | 99: Suitable for Nested PCR | | | | |
| Time Up / Down | 0-9min59sec, Suitable for Long PCR | | | | |
| Temp. Up / Down | 0.1-9.9°C, Suitable for Touchdown PCR | | | | |
| Auto Pause / Power Protection | Yes | | | | |
| Soak Function | Yes | | | | |
| Gradient Range | 30-105°C | - | 30-105°C | - | - |
| Gradient Range of Temp. Differential | 1-30°C | - | 1-30°C | - | - |
| Hot Lid Temp. Range | 30-110°C | | | | |
| Height of Hot Lid | Stepless Adjustable | | | | |
| Auto Shut-Off Function of Hot Lid | When block is below the setting temp. or after finish running, hot lid will be auto shut-off | | | | |
| Port | USB | | | | |
| Communication Interface | LAN | | | | |
| Input Power | 100-240V, 50-60Hz | | | | |
| Output Power | 600W | | | | |
| Dimensions | 368×250×285mm | | | | |
| Net Weight | 10.5kg | | | | |