

WaterVac 100 Vacuum Filtration System



Features

- ▶ **Save 70% bench space**
The compact design of WaterVac 100 vacuum filtration system can save much bench space by simplifying procedure and tools needed in membrane filtration method.
- ▶ **Improve operation time**
Direct drainage design saves a lot of time to empty waste bottle and make the filtration more efficient.
- ▶ **Versatile**
Replaceable funnel adaptor design makes WaterVac 100 compatible with various kinds of filter holder.
- ▶ **Compatible with Rocker SF funnel**
WaterVac 100 - MB can accept Rocker SF funnel - 100 / 300 / 500 ml. SF funnel is made of SS316 stainless steel which can be fast sterilized by flame.
- ▶ **International certification**
CE certification
- ▶ **One-Year Warranty**

Applications

- ▶ Microbiological test
- ▶ Vacuum filtration

Ordering Information

190100-01(02)

WaterVac 100, Vacuum Filtration System with AC100~240V adaptor, US plug (EU plug)

190120-01(02)

WaterVac 100 - MB, Vacuum Filtration System with Rocker SF funnel adaptor, AC100~240V adaptor, US plug (EU plug)

190121-01(02)

WaterVac 101 - MB, Vacuum Filtration System with Rocker SF funnel adaptor, 100 ml SF funnel, AC100~240V adaptor, US plug (EU plug)

180100-01

SF, 100 ml Stainless Steel Funnel

180100-03

SF, 300 ml Stainless Steel Funnel

180100-05

SF, 500 ml Stainless Steel Funnel

WaterVac 100 - MB



WaterVac 101 - MB



Specification

Model	WaterVac 100	
Power	DC12V, 1.0A	
Max. vacuum	313 mbar	
Max. liquid flow rate	0.5 L/min	
Motor	12W Brushless DC Motor	
Hose barb	ID6	
Material contact with filtrate	SS316, FKM, Silicone, PP, PA66	
Weight	1.16 Kg	
Dimension (LxWxH)	17 x 12 x 9.6 cm	
	WaterVac 100 - MB	WaterVac 101 - MB
Number of branch	1	1
Adaptor	Spin-lock design	Spin-lock design
Funnel	SF stainless steel funnel, 100 / 300 / 500 ml (optional)	SF stainless steel funnel, 100 ml (standard)