

# Filtration Accessories



## PES / PC Vacuum Bottle

Specification	1200 ml, PES vacuum bottle	1200 ml, PC vacuum bottle
Catalog number	197000-11	197000-11-PC
Graduated increment	100 ml	100 ml
Overflow protection	Yes	Yes
Cap with suction fitting	Yes	Yes
Hose barb	ID8	ID8
Autoclavable	Yes	Yes



## PP Heavy-Duty Vacuum Bottle **NEW**

Specification	4000 ml, PP vacuum bottle	4000 ml, PP vacuum bottle with drain
Catalog number	197200-47	197200-48
Connector	Hose barb	Hose barb
Graduated increment	500 ml	500 ml
Overflow protection	Yes	Yes
Hose barb	ID4 ~ ID8	ID4 ~ ID8
Drain device	-	Yes
Autoclavable	Yes	Yes



## Multilayer Filtration Adaptor **NEW**

Specification	Multilayer filtration adaptor
Catalog number	167230-05
Main material	Borosilicate glass
Material of membrane support	SS screen
Filter diameter	47 mm
Filter holder	300 ml glass filter holder (optional)



## Continuous Filtration Kit **NEW**

Specification	Continuous filtration kit
Catalog number	167210-36
Main material	PTFE
Material of hose barb	PTFE
Filter holder	300 ml glass filter holder (optional)
Hose barb	ID6



\* PES : Polyethersulfone, PC : Polycarbonate, PP : Polypropylene

# Filtration Accessories



## Membrane Filters

Specification	Glass fiber filter	MCE membrane
Catalog number	167100-20	167100-52
Brand	Pall	Pall
Filter diameter	47 mm	47 mm
Pore size	1µm	0.45µm
Material of filter	Glass fiber	MCE
Package	100/PK	200/PK



## GL45 Suction Cap / Filtration Adaptor

Specification	GL45 suction cap	GL45 filtration adaptor
Catalog number	197000-60	197000-65
Material of cap	PP	PP
Material of gasket	-	PTFE
Stopper	-	No.8 stopper
Hose barb	ID6	ID4 ~ ID8
Autoclavable	Yes	Yes

### Application for GL45 Suction Cap

#### Waste Bottle

Suitable for collecting waste media by using GL45 bottle in connection with suction pump and accessories.




#### Moisture Trap Bottle

Available to absorb moisture with desiccant which turns pink when saturated.



#### Vapor Absorption (Neutralization) Bottle

Ideal for absorbing acid or alkaline vapor to prevent harmful vapors from spreading into the environment or pump.



#### Safety Bottle

Works as a safety bottle to prevent liquid from being sucked into pump.



\* Please refer to P.66 to select GL45 Laboratory Glass Bottle