

WL-CBE/AD

WEEPRO OVERBOOTS WITH ANTI SLIP SOLE - Type PB 6B

Personal Protective Equipment Cat.III

FEATURES & BENEFITS

- Very low-linting fabric that prevents any contamination in a controlled critical environment
- Thick PVC sole with strong anti-slip properties on dry or wet floors
- Elastic tightening under the knee and securing tie at the calf level
- Boot height of 50 CM to cover up to the knee to protect the most exposed areas
- Antistatic treated material facilitating the dissipation of electrostatic charges (only on the microporous fabric)
- Ideal protection against projection of low-concentration chemicals, powders, adhesives, fiberglass, solvents, paints.
- Two sizes available: S/M – L/XL



PRODUCT DETAILS

Product Name :	Weepro Overboots
Product Type :	Type PB 6B
Fabric :	Microporous film
Grammage :	63 g/m ²
Confection :	Elastic strap under the knee Ankle support strap PVC sole with antislip properties
Coutures :	4-thread overlock
Color :	White
Qty / case :	15 polybags x 20 units
Origin :	China

CERTIFICATIONS & STANDARDS

- Complies with the requirements of Regulation (EU) 2016/425 on Personal Protective Equipment
- Manufactured under an ISO 9001 certified system

PHYSICAL PROPERTIES OF THE FABRIC		
Tests	Test method	Results
Abrasion resistance	EN 530	Classe 1/6
Flex cracking resistance	ISO 7854 B	Classe 4/6
Tear resistance	ISO 9073-4	Classe 2/6
Tensile strength	ISO 13934-1	Classe 1/6
Puncture resistance	EN 863	Classe 1/6
Seam strength	EN ISO 13935-2	Classe 3/6

FABRIC RESISTANCE TO PENETRATION BY LIQUIDS EN ISO 6530		
Chemicals tested	Penetration	Repellency
Sulphuric Acid 30%	Classe 3/3	Classe 3/3
Sodium Hydroxide 10%	Classe 3/3	Classe 3/3
O-Xylene	Classe 3/3	Classe 2/3
Butan-1-ol	Classe 3/3	Classe 3/3

FABRIC RESISTANCE TO PENETRATION BY INFECTIVE AGENTS EN 14126	
Resistance to penetration by contaminated liquids under hydrostatic pressure ISO 16604 / ISO 16603	Classe 6/6
Resistance to penetration by contaminated liquids according to EN ISO 22610	Classe 6/6
Resistance to penetration by contaminated liquid aerosols according to EN ISO 22611	Classe 3/3
Resistance to penetration by contaminated solid particles ISO 22612	Classe 3/3

STORAGE CONDITIONS

Normal storage and conservation conditions: Should not be exposed to moisture and sunlight, and should be stored at room temperature.

LOGISTICS



**Outer case
Spec.**

Item	Size Mm	Gross weight (kg)	Qty / pallet
WL-CBE/AD-SM	600 x 280 x 430	11	20
WL-CBE/AD-LXL		13	

**Inner bag
Spec.**

Packaging
15 polybags x 20 units

EAN Codes

Item	Outer case
WL-CBE/AD-SM	3 701 012 801 179
WL-CBE/AD-LXL	3 701 012 801 964