



Overboot without anti-slip sole

## Standards



EN ISO  
1149-5

EN ISO  
14126

## Technical Specifications




Under-knee  
elastic wrap

Holding string at  
calf


- Very low lint material to prevent all contamination in a controlled critical environment
- Under-knee elastic wrap
- 50 cm high overboot to protect the most exposed parts up to the knee
- Antistatic treatment to allow easy dissipation of electrostatic charges
- Ideal protection against : splashes of low concentration chemicals, powders, adhesives, glassfibers, solvents, paints

# Material and Seam

## MICROPOROUS FILM MATERIAL



## STITCHED SEAMS



4 THREADS

## Applications

- Interventions on asbestos sites
- Composite industries
- Food industries
- Pharmaceutical and cosmetic laboratories in white room environment
- Cleaning and site maintenance

## Technical data

### Resistance to liquid penetration

#### Chemical properties of the material EN 368

H<sub>2</sub>SO<sub>4</sub> - Sulfuric acid 30%  
NaOH - Sodium Hydroxide 10%  
O Xylene  
Butan-1-ol

#### Penetration

Class 3  
Class 3  
Class 3  
Class 3

#### Repulsion

Class 3  
Class 3  
Class 2  
Class 3

## Reference

One Size

WL-CBE/NAD-00



X300

