

DATA SHEET WEEPRO OVERSHOES ANTI SLIP SOLE

REF :WL-CCE/AD-00



FEATURES: Microporous Film Over shoes with anti-slip model. Elasticated top and heel. PVC Anti-slip sole.

FABRICS AND SEAMS : White Microporous film 63^{GSM} - PVC 370^{GSM}- Serged seams

PHYSICAL PERFORMANCE

Fabric Physical Properties	Test Method	Résultats	Class
Abrasion resistance	EN530	>400 cycles	Class 3
Flex cracking	ISO 7854 B	>50 000 cycles	Class 6
Trapezoidal Tear	ISO 9073-4	61.5 N / 28.4 N	Class 2
Tensile strength	ISO 13934-1	109 N / 47.4 N	Class 1
Puncture resistance	EN863	9.06 N	Class 1

FABRIC RESISTANCE TO PENETRATION BY LIQUIDS EN ISO 6530

Fabric Chemical Properties	Penetration	Repellency
Sulphuric Acid 30%	Class 3	Class 3
Sodium Hydroxide 10%	Class 3	Class 3
O-Xylène	Class 3	Class 2
Butan-1-ol	Class 3	Class 3

CATEGORY 3 TYPE PB: PARTIAL BODY

Dry particles Type PB 5 Method as defined by EN ISO 13982-1:2004 + A1:2010	Pass
Light splashes Type PB 6 Method as defined by EN 13034: 2005 +A1: 2009	Pass
Barrier to infective agents EN14126: 2003	Pass
Protection factor according to EN 1073-2:2002	Class 1
Surface resistivity EN 1149-5 / The slip-retardant sole is not antistatic treated.	Pass

CHART SIZE

Size	WeeSafe reference	LENGHT	WIDTH
XS	WL-CCE/AD-XS	27 CM	11.5 cm
SM	WL-CCE/AD-SM	30 CM	11.5 cm
LXL	WL-CCE/AD-LXL	36 CM	11.5 cm

PACKAGING

	Units	Weight	Size	Volume
Carton	400	13 KG	47 X 32 X 45 CM	0,0676 ^{M3}
Pallet	6 000	195 KG	80 X 120 CM	1.01 ^{M3}

GENCOD : 3701012802015

CUSTOM CODE : 6307909800

WeeSafe – 1 rue du Centre « Immeuble le Fujy » - 93160 Noisy le Grand Tél : + 33 (0)1 43 09 98 04
Courriel : contact@weesafe.fr