

Immersion Cooler with air-cooled refrigerating unit. Housing of stainless steel with 2 handles, condensing probe of stainless steel, flexible cooling connection line in special single-tube construction, protective hose with smooth surface. The refrigeration unit works continuously.

Technical data according to DIN 12876

Operating temperature range	-50...50 °C
Cooling power	-
at 0°C	0,3 kW
at -20°C	0,26 kW
at -30°C	0,2 kW
Safety classification	Class I / NFL
Refrigeration machine	air-cooled, natural refrigerant
Refrigerant	R290
Refrigerant quantity	0,06 kg
Gas warning sensor	without
Nominal diameter probe	48 mm
Length of probe	155 mm
Length flexible connection	1150 mm
Overall dimensions WxDxH **	260x330x415 mm
Net weight	25 kg
Power supply requirement	230V 1~ 50/60Hz
max. current	3 A
min. Fuse (1 phase)	10A
max. Fuse (1 phase)	16A
min. ambient temperature	5 °C
max. ambient temperature	40 °C



Order-No.: 3004.0001.99

from Serial-No.:

109458

1.2/10

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

Output data valid for: Room temperature 20° C
in accordance with EN60034-1 the following voltage and frequency tolerances are valid:
Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%
Example -5% voltage and + 2% frequency -> not allowed!
-5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility:
Classification (disturbance) to EN55011: Class A, Group 1

- Standard delivery conditions - Power cable configuration:
1. Single-phase devices (230V/115V) -> with cable and plug
 2. Three-phase devices with current consumption less than 63A -> with cable, without plug
 3. Three-phase devices with current consumption greater than 63A -> without cable, without plug

** Please respect space requirements. See operating conditions at www.huber-online.com