




CO₂ Incubator

ICO240med

Safety at all times: High-end functions for the protection of cell cultures, bacteria cultures or tissue cultures.



On this page, you can find all the essential technical data on the Memmert CO₂ incubator ICOmed. Our customer relations team will be pleased to help if you want further information. If you should require a customised special solution, please contact our technical specialists at myAtmoSAFE@memmert.com.



Temperature

Working-temperature range	5 °C above ambient temperature up to +50 °C Standard sterilisation programme: 60 minutes at 180°C (without removing the sensors)
Setting temperature range	+18 to +50 °C
Setting accuracy temperature	0.1 °C
Temperature sensor	2 Pt100 sensors DIN Class A in 4-wire-circuit for mutual monitoring, taking over functions in case of an error

Humidity

Humidity control (standard)	Humidity limitation thanks to a Peltier element; when water dish is full and inserted, the Peltier element limits the value of relative humidity in the interior to 93 % rh +/- 2.5 %
Setting accuracy humidity	0.5 % rh
Setting range active humidity control (with option K7)	40 to 97 % rh and rh-Off

Control of standard components

CO2 control	Digital electronic CO2 control with dual beam NDIR system, with auto-diagnostic system and acoustic fault indication, barometric pressure compensation
Adjustment range CO2	0 to 20 % CO2
Setting accuracy CO2	0,1%
Variation in time CO2	+/- 0.2 % CO2
Adjustment range O2 (with option T6)	1 to 20 % O2
Setting accuracy O2	0.1 % O2

Control technology

ControlCOCKPIT	TwinDISPLAY. Adaptive multifunctional digital PID-microprocessor controller with 2 high-definition TFT-colour displays.
Language setting	German, English, Spanish, French, Polish, Czech, Hungarian
Function SetpointWAIT	the process time does not start until the set temperature is reached
Adjustable parameters	temperature (Celsius or Fahrenheit), CO2, programme time, time zones, summertime/wintertime

Communication

Interface	Ethernet LAN, USB
Documentation	programme stored in case of power failure
Programming	AtmoCONTROL software on a USB stick for programming, managing and transferring programmes via Ethernet interface or USB port

Safety

AutoSAFETY

additionally integrated over- and undertemperature protection "ASF", automatically following the setpoint value at a preset tolerance range, alarm in case of over- or undertemperature, heating function is switched off in case of overtemperature, cooling function in case of undertemperature

Autodiagnostic system

integral fault diagnostics for temperature and CO2

Alarm

visual and acoustic

Heating concept

6 sides

large-area multi-function heating system on four sides with additional door and back heating to avoid condensation

Standard equipment

Standard accessories

Membrane filter (in order to remove impurities and pollutants, all incoming gases pass through a membrane filter before they reach the chamber)

Door

fully insulated stainless steel door with 2-point locking (compression door lock)

Internals

2 perforated stainless steel shelf/shelves

Works calibration certificate

incl. works calibration certificate (measuring point chamber centre) at +37°C, 5 % CO2 for standard units

Internals

1 stainless steel water dish

Door

inner glass door with opening (8 mm Ø) to take gas sample

Stainless steel interior

Dimensions

$w_{(A)} \times h_{(B)} \times d_{(C)}$: 600 x 810 x 500 mm (d less 35 mm for fan)

Interior

material 1.4301 (ASTM 304), corrosion resistant

Volume

241 l

Max. number of internals

12

Max. loading of chamber

140 kg

Max. loading per internal

15 kg

Textured stainless steel casing

Dimensions

$w_{(D)} \times h_{(E)} \times d_{(F)}$: 759 x 1180 x 691 mm (d +56mm door handle)

Housing

rear zinc-plated steel

Electrical data

Voltage

230 V, 50/60 Hz

Electrical load

approx. 1650 W

Voltage

115 V, 50/60 Hz

Electrical load

approx. 1650 W

Ambient conditions

Set Up

The distance between the wall and the rear of the appliance must be at least 15 cm. The clearance from the ceiling must not be less than 20 cm and the side clearance from walls or nearby appliances must not be less than 5 cm.

Ambient temperature	10 °C to 35 °C
Humidity rh	max. 70 %, non-condensing
Altitude of installation	max. 2,000 m above sea level
Overvoltage category	II
Pollution degree	2

Packing/shipping data

Transport information The appliances must be transported upright

Customs tariff number 8419 8998

Country of origin Federal Republic of Germany

WEEE-Reg.-No. DE 66812464

Dimensions approx incl. carton w x h x d: 840 x 1360 x 900 mm

Net weight approx. 110 kg

Gross weight carton approx. 145 kg

Standard units are safety-approved and bear the test marks

