

SHOWA
BO700

Ideal for specialized industries where cleanliness is a priority, this glove has a flexible PVC coating that provides chemical resistance and excellent gripping action.

[**FEATURES**

- Unsupported PVC
- 300 mm (12 in.) long
- 12 mil (0,39 mm) thick
- Embossed finish
- Clean white color

[**BENEFITS**

- Fits like second-skin and provides unrivaled softness
- The patterned palm and fingertips provide excellent gripping action
- The slip on treatment makes gloves easily slip on or off
- Excellent alternative to natural rubber gloves that may cause allergies

[**INDUSTRY**



Aerospace



Automotive



Electronics



Engineering

[**IDEAL APPLICATIONS**

- Intricate parts handling
- Mechanical and engineering
- Painting and spray workshops
- Integrated circuits
- Semiconductors



MATERIAL

- Unsupported

COATING

- PVC

GRIP

- Embossed

STANDARDS



EN 374-2:2003



EN 388:2016



2000X

EN ISO 374-1:2016/Type C



KL

DOMINIQUE OUTLET

SHOWA
BO700



- PACKAGING**
- 10 Pair per polybag
 - 24 Polybags per case
 - 240 Pair per case

- COLOUR**
- White

- SIZES**
- S
 - M
 - L
 - XL

- THICKNESS**
- 12 mil



[YOU MIGHT ALSO BE INTERESTED IN

SHOWA
BO600



MATERIAL
Nylon

COATING
Polyurethane

SHOWA
BO500W



MATERIAL
Nylon

COATING
Polyurethane

SHOWA
BO500B



MATERIAL
Nylon

COATING
Polyurethane

[USER INSTRUCTIONS

Protection against mechanical risks, with electrostatic properties. Do not use where there are electrical, thermal or entanglement risks. Wash at 40°C max. Performance levels as per standard EN388 retained after 3 washes, subject to variations linked to actual usage conditions. The performance levels apply to the coated surface only. Store in a dry place, away from the light. All clothing and shoes worn with the glove with electrostatic dissipation properties must also be designed taking the electrostatic risk into account.

[DISCLAIMER

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.

Get in touch

SHOWA USA | 579 Edison Street - Menlo, GA 30731, USA

USA@SHOWAgroup.com

© SHOWA Group 2018 | All rights reserved