

SPECTROLINE®

E Series

Handheld UV Lamp

EA-140 + EA-160



Forensics



Lab &
LifeSciences



Mineral
Inspection

TOGGLE SWITCH

Built in toggle switch for easy On/Off operation

ERGONOMIC CARRYING HANDLE

Comfortable grip while operating the lamp.

ANODIZED ALUMINUM HOUSING

Lightweight and rugged for the toughest work environments.

BUILT IN REFLECTORS

Corrosion resistant, aluminum reflectors intensify the high UV output.





EA-140 E SERIES HANDHELD UV LAMP

EA-160 E SERIES HANDHELD UV LAMP



	EA-140	EA-160
Light Source:	UV-A Tube	UV-A Tube
Lamp Style:	Handheld Lamp	Handheld Lamp
Power:	4 Watts	6 Watts
Length:	7 in (17.8 cm)	10.25 in (26.03 cm)
Width:	3.25 in (8.25 cm)	3.25 in (8.25 cm)
Height:	2.5 in (6.35 cm)	2.5in (6.35 cm)
Weight:	2.45 lb (1.1 kg)	2.7 lb (1.22 kg)
Plug Options:	USA, Australian (/FA), United Kingdom (/FBE), China (/FC), European (/FE), Japan(/J), 12 Volt (/12)	



DISTRIBUTED BY:

www.Spectro-UV.com
 4 Dubon Ct., Farmingdale, NY 11735
 866-230-7305