



Bel-Art Products, a part of SP  
661 Route 23 South, Wayne, New Jersey 07470  
Tel: 973-694-0500 \* Fax: 973-694-7199  
[www.sp-belart.com](http://www.sp-belart.com)

## CERTIFICATE OF ANALYSIS

This is to verify that all items noted below are in conformance with the Purchase Order Contract, drawings, specifications, and other applicable documentation; that all process certifications, material certifications, are on file at this or another Bel-Art facility and are available for review by the customer and or Government Representatives upon request.

**Product #:** 42074-1220      **Mfg. Date:** N/A      **Lot #:** GENERAL

**Description:** SECADOR 4.0 Vertical Auto Desiccator Cabinets 230V  
Patented, Made in USA

**Material:** Co-polyester, Polystyrene, Polycarbonate, Silicone Rubber, Steel rods and latches  
Closed Cell EPDM door Gaskets, Circuit board, Silica gel beads

**Dimensions:** Overall 20.4" H x 13.4" W x 16.3" D, Inside Dimensions (approx.) 17.5"H x 11.5"W x 13.75D  
Interior volume 1.9 cu. ft., 3.75" minimum between shelves, Approx. wt. 23.9 lbs.

**Other:** Input: 230 Volt 50HZ 0.23A, Output 24.0VAC, 20VA minimum, 833mA minimum  
Hygrometer in door can be calibrated, Reduces RH from 75% to <25% in 8 hours at  
room temperature, Loop for tamper resistant seal or padlock, Padlocks not Provided,  
Gas ports not available on electric units-completely clear, blocks 99% UV light  
Product has been CE, CSA, CETL Certified

Manufactured by: Bel-Art Products, a part of SP  
2024 Broad Street Pocomoke City, MD 21851  
An ISO-9001:2015 facility (certificate US19/819943409)  
Made in the USA

Reviewed and Approved By:

Signature:

**Printed Name:** Nancy K. Trogani

**Title:** Technical Support Analyst

**Date:** 10/14/2021

